



Be Right™



Flow cell for 1" NPT sensor

Productnr.:	7300800
EUR Prijs:	Neem contact op
Beschikbaar:	

The flow cell can be used for either the pH/D and NH₄D (ammonium ISE) or NO₃D (nitrate ISE) sensors. The flow cell has many features and benefits. A clear body enables quick inspection of the sensor and accumulated debris. Complete Sensor Immersion ensures good temperature compensation. Quick disconnects enable easy removal of the sensor for service. Large Porting, 3/8 inch inlet and 1/2 inch outlet, minimizes flow cell plugging due to debris. Tangential Inlet Porting introduces a vortex in the flow stream. This vortex separates heavy particles and ensures good mixing of process fluid inside the flow cell.